



WRSO100PSB

115/230V Shaver Outlet Polished Steel Black Insert

Technical characteristics

Architecture

Fixing mode	flush-mounting
Number of poles	2pole

Main electrical features

Nominal voltage	250 V AC
Rated current	≈ 87...174 mA

Dimensions

Depth	54.5 mm
Height	146 mm
Width	86 mm

Cover, door

Cover	Full cover plate
-------	------------------

Materials

Material	stainless steel
----------	-----------------

Connection

Type of connection	screw
Type of connection	with screw terminals

Safety

Protection index IP	IP20
Protection	Enhanced contact protection

Use conditions

Insert	insert, black
--------	---------------