



WRSO100PSW



**IP20**

**115/230V Shaver Outlet Polished Steel White Insert**

**Technical Characteristics**

**Architecture**

Fixing mode	flush-mounting
Number of poles	2pole

**Main electrical features**

Nominal voltage	250 V
Rated voltage	220...230 V AC
Rated current	≈ 87...174 mA
Rated current	174 mA

**Dimensions**

Depth	54.5 mm
Height	146 mm
Width	86 mm

**Capacity**

Number of modules	0
-------------------	---

**Cover, door**

Cover	Full cover plate
-------	------------------

**Materials**

Colour	silver optics
Material	stainless steel
Surface appearance	glossy
Type of surface treatment	Other
Colour syntax: Colour	silver

**Installation, mounting**

Imprint	with imprint
---------	--------------

**Connection**

Type of connection	screw
Type of connection	with screw terminals

**Cable**

Wiring	with double earth connection
--------	------------------------------

**Scope of delivery**

Component	with 2 fixing screws M3.5 x 30 mm
-----------	-----------------------------------

**Safety**

Protection index IP	IP20
Protection	Enhanced contact protection

**Use conditions**

Insert	insert white
--------	--------------

**Identification**

Designation syntax: Core  
designation/function

Socket outlet without earthing contact