



WRSS81BNB



13A 1 Gang Double Pole Switched Socket Black Nickel Black Insert

Technical Characteristics

Fixing mode	flush-mounting
Nominal voltage	250 V
Rated voltage	220...230 V AC
Rated current	13 A
Rated current	13 A
Depth	25.8 mm
Height	86 mm
Width	86 mm
Number of modules	0
Cover	Full cover plate
Colour	black
Material	stainless steel
Surface appearance	matt
Type of surface treatment	Nickel-plated
Colour syntax: Colour	black
Inprint	without imprint
Type of connection	screw
Wiring	with earth connection
Component	with 2 fixing screws M3.5 x 30 mm
Protection index IP	IP20
Protection	Enhanced contact protection
Insert	insert, black
Designation syntax: Core designation/function	socket outlet