



WRSS81PSW



13A 1 Gang Double Pole Switched Socket Polished Steel White Insert

Technical characteristics

Electric current

Rated current	13 A
---------------	------

Voltage

Rated voltage	250 V
---------------	-------

Nominal voltage	250 - 250 V
-----------------	-------------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Mounting type	Screw mounting
---------------	----------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Dimensions

Height	86 mm
--------	-------

Width	86 mm
-------	-------

Depth	25.80 mm
-------	----------

Materials

Colour	Silver
--------	--------

Surface finish	Glossy
----------------	--------

Material	Stainless steel
----------	-----------------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Equipment

Connector/plug type socket outlet	British Standard
-----------------------------------	------------------

Rotated central insert	No
------------------------	----

With hinged lid	No
-----------------	----

With round protective earth pin	No
---------------------------------	----

With signal lamp	No
------------------	----

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	0
-------------------	---

Texts

Imprint	Without imprint
Cover	Full cover plate
Wiring	With earth connection
Protection	Enhanced contact protection