



WRSS82BNB-USBS

13A 2 Gang Double Pole Switched Socket c/w Twin USB Ports Black Nickel Black

Technical characteristics

Main electrical features

Nominal voltage	250 V
Rated voltage	220...230 V AC

Dimensions

Depth	39.1 mm
Height	86 mm
Width	146 mm

Cover, door

Cover	Full cover plate
-------	------------------

Materials

Surface appearance	matt
--------------------	------

Connection

Type of connection	screw
--------------------	-------

Cable

Wiring	with double earth connection
--------	------------------------------

Scope of delivery

Component	with 2 fixing screws M3.5 x 30 mm
-----------	-----------------------------------

Safety

Protection	Enhanced contact protection
------------	-----------------------------

Use conditions

Insert	insert, black
--------	---------------