



WRSS82BNB-USBS

13A 2 Gang Double Pole Switched Socket c/w Twin USB Ports Black Nickel Black

Technical characteristics

Architecture

Fixing mode flush-mounting

Main electrical features

Nominal voltage 250 V

Rated voltage 220...230 V AC

Dimensions

Depth 39.1 mm

Height 86 mm

Width 146 mm

Cover, door

Cover Full cover plate

Materials

Colour black

Material stainless steel

Surface appearance matt

Type of surface treatment Nickel-plated

Connection

Type of connection screw

Cable

Wiring with double earth connection

Scope of delivery

Component with 2 fixing screws M3.5 x 30 mm

Safety

Protection index IP IP20

Protection Enhanced contact protection

Use conditions

Insert insert, black