



WRSS82BSB

13A 2 Gang Double Pole Switched Socket Brushed Steel Black Insert

Technical characteristics

Architecture

Fixing mode flush-mounting

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Rated current 13 A

Dimensions

Depth 29 mm

Height 86 mm

Width 146 mm

Cover, door

Cover Full cover plate

Materials

Colour stainless steel optics

Material stainless steel

Surface appearance matt

Type of surface treatment brushed

Connection

Type of connection screw

Safety

Protection index IP IP20

Protection Enhanced contact protection

Use conditions

Insert insert, black