



WRSS82BSB-USBAC

DP Switched Socket 13A 2G USB A+C ports Brushed Steel Black Raised

Technical characteristics

Architecture

Fixing mode flush-mounting

Main electrical features

Rated voltage 220...240 V AC

Dimensions

Depth 18 mm

Height 86 mm

Width 146 mm

Cover, door

Cover Full cover plate

Materials

Colour stainless steel optics

Material stainless steel

Surface appearance matt

Type of surface treatment brushed

Connection

Type of connection screw

Safety

Protection index IP IP20

Protection Enhanced contact protection

Use conditions

Insert insert, black