



WRSS82BSW-USBAC

## DP Switched Socket 13A 2G USB A+C ports Brushed Steel White Raised

### Technical characteristics

#### Architecture

Fixing mode flush-mounting

#### Main electrical features

Rated voltage 220...240 V AC

#### Dimensions

Depth 18 mm

Height 86 mm

Width 146 mm

#### Cover, door

Cover Full cover plate

#### Materials

Colour stainless steel optics

Material stainless steel

Surface appearance matt

Type of surface treatment brushed

#### Connection

Type of connection screw

#### Cable

Wiring with double earth connection

#### Scope of delivery

Component with 2 fixing screws M3.5 x 30 mm

#### Safety

Protection index IP IP20

Protection Enhanced contact protection

#### Use conditions

Insert insert white