



WRSS82PBB

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Main electrical features

Nominal voltage	250 V
Rated voltage	220...230 V AC
Rated current	13 A

Dimensions

Depth	29 mm
Height	86 mm
Width	146 mm

Materials

Material	stainless steel
Type of surface treatment	Anodised

Connection

Type of connection	screw
--------------------	-------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Insert	insert, black
--------	---------------