



WRSS82PBW

### 13A 2 Gang Double Pole Switched Socket Polished Brass White Insert

#### Technical characteristics

##### Architecture

Fixing mode	flush-mounting
-------------	----------------

##### Main electrical features

Nominal voltage	250 V
Rated voltage	220...230 V AC
Rated current	13 A

##### Dimensions

Depth	29 mm
Height	86 mm
Width	146 mm

##### Cover, door

Cover	Full cover plate
-------	------------------

##### Materials

Material	stainless steel
Type of surface treatment	Anodised

##### Connection

Type of connection	screw
--------------------	-------

##### Safety

Protection index IP	IP20
Protection	Enhanced contact protection

##### Use conditions

Insert	insert white
--------	--------------