



WRSS82PSB

13A 2 Gang Double Pole Switched Socket Polished Steel Black Insert

Technical characteristics

Architecture

Fixing mode flush-mounting

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Rated current 13 A

Dimensions

Depth 29 mm

Height 86 mm

Width 146 mm

Cover, door

Cover Full cover plate

Materials

Colour silver optics

Material stainless steel

Surface appearance glossy

Type of surface treatment Other

Connection

Type of connection screw

Cable

Wiring with double earth connection

Scope of delivery

Component with 2 fixing screws M3.5 x 30 mm

Safety

Protection index IP IP20

Protection Enhanced contact protection

Use conditions

Insert insert, black