



WRSS82PSW-USBAC



DP Switched Socket 13A 2G USB A+C ports Polished Steel White Raised

Technical characteristics

Electric current

Rated current	13 A
---------------	------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Voltage

Nominal voltage	230 - 230 V
-----------------	-------------

Connectivity

Connector/plug type USB	AC
Type of connection	Screw terminal
Mounting type	Screw mounting

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Dimensions

Built-in depth flush-mounted boxes	25 mm
Height	86 mm
Width	146 mm
Depth	18 mm

Materials

Surface finish	Glossy
Material	Stainless steel

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Texts

Imprint	With imprint
Cover	Full cover plate
Wiring	With double earth connection
Protection	Enhanced contact protection