



WRSS82PSW-USBS

### 13A 2 Gang Double Pole Switched Socket c/w Twin USB Ports Polished Steel White

#### Technical characteristics

##### Architecture

Fixing mode	flush-mounting
-------------	----------------

##### Main electrical features

Nominal voltage	250 V
Rated voltage	220...230 V AC

##### Dimensions

Depth	39.1 mm
Height	86 mm
Width	146 mm

##### Cover, door

Cover	Full cover plate
-------	------------------

##### Materials

Type of surface treatment	Other
---------------------------	-------

##### Cable

Wiring	with double earth connection
--------	------------------------------

##### Scope of delivery

Component	with 2 fixing screws M3.5 x 30 mm
-----------	-----------------------------------

##### Safety

Protection index IP	IP20
Protection	Enhanced contact protection

##### Use conditions

Insert	insert white
--------	--------------