



WRTVLPBHSW



2G Lounge Plate For TV, Power & Data Raised Brushed Steel White

Technical characteristics

Electric current

Rated current	13 A
---------------	------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Nominal voltage	250 - 250 V
-----------------	-------------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Mounting type	Screw mounting
---------------	----------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Dimensions

Built-in depth flush-mounted boxes	47 mm
------------------------------------	-------

Height	172 mm
--------	--------

Width	146 mm
-------	--------

Depth	1.50 mm
-------	---------

Materials

Surface finish	Glossy, Mat
----------------	-------------

Material	Stainless steel
----------	-----------------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Equipment

Connector/plug type socket outlet	British Standard
-----------------------------------	------------------

Rotated central insert	No
------------------------	----

With hinged lid	No
-----------------	----

With round protective earth pin	No
---------------------------------	----

With signal lamp	No
------------------	----

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	8
-------------------	---

Texts

Imprint	Without imprint
Cover	Full cover plate
Protection	Enhanced contact protection