



WXPDP842



## IP66 20A 2 Gang 1 Way Double Pole Switch

### Technical characteristics

#### Electric current

Rated current	20 A
---------------	------

#### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

#### Voltage

Rated voltage	250 V
---------------	-------

#### Materials

Colour	Light grey
Surface finish	Mat
Material	Polycarbonate (PC)
Treatment	Untreated

#### Identification

Assembly arrangement	Basic element with complete housing
----------------------	-------------------------------------

#### Connectivity

Mounting type	Screw mounting
---------------	----------------

#### Controls and indicators

Number of buttons	1
-------------------	---

#### Dimensions

Built-in depth	0
----------------	---

#### Safety

Ingress Protection (IP) class	IP66
-------------------------------	------

#### Architecture

Control/operation element	Double rocker
---------------------------	---------------

#### Texts

Lighting	Without lighting (cannot be illuminated)
Switch mode	2-pole