



WXPPS12



IP66 10AX 1 Gang 2 Way Switch

Technical characteristics

Electric current

| | |
|-------------------|------|
| Switching current | 10 A |
| Rated current | 10 A |

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Materials

| | |
|----------------|--------------------|
| Colour | Light grey |
| Surface finish | Mat |
| Material | Polycarbonate (PC) |
| Treatment | Untreated |

Identification

| | |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with complete housing |
|----------------------|-------------------------------------|

Connectivity

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Controls and indicators

| | |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP66 |
|-------------------------------|------|

Architecture

| | |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

Texts

| | |
|-------------------|--|
| Installation mode | For flush-mounted and hollow wall mounting |
| Lighting | Without lighting (cannot be illuminated) |
| Switch mode | 2-way |