



WXPPS12B



IP66 10A 1 Gang Press Bell Switch

Technical characteristics

Electric current

Momentary contact current	10 A
---------------------------	------

Voltage

Rated voltage	250 V
---------------	-------

Architecture

Number of poles	2
-----------------	---

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Controls and indicators

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

Materials

Colour	Light grey
Surface finish	Mat
Material	Polycarbonate (PC)
Treatment	Untreated
Transparent	No

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Dimensions

Depth	50 mm
-------	-------

Safety

Ingress Protection (IP) class	IP66
-------------------------------	------

Texts

Imprint	Without imprint
---------	-----------------