



WXPS82



IP66 Twin 13A Un-switched Socket

Technical characteristics

Electric current

Rated current	13 A
---------------	------

Voltage

Rated voltage	250 V
---------------	-------

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

Safety

Ingress Protection (IP) class	IP66
-------------------------------	------

Dimensions

Height	116.50 mm
Width	146 mm
Depth	88.25 mm

Materials

Colour	Light grey
Surface finish	Glossy
Material	Polycarbonate (PC)

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	No
With signal lamp	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	0
-------------------	---

Texts

Imprint	Without imprint
---------	-----------------

Cover	Full cover plate
Wiring	With double earth connection
Protection	Enhanced contact protection
Cover, door	
Type of lid	Hinged cover falls back, manual clip-in