



WXPSS81EV

## IP66 Single 13A Double Pole Switched Socket for Electric Vehicle

### Technical characteristics

#### Architecture

Fixing mode surface-mounting

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Rated current 13 A

#### Dimensions

Depth 88.25 mm

Height 86 mm

Width 86 mm

#### Cover, door

Cover Full cover plate

#### Materials

Colour blue

RAL colour RAL 5009 - Azure blue

Material Polycarbonate (PC)

Surface appearance matt

Type of surface treatment untreated

#### Connection

Type of connection screw

#### Cable

Wiring with earth connection

#### Safety

Protection index IP IP66

Protection Enhanced contact protection