



WXPSS82



## IP66 Twin 13A Double Pole Switched Socket

### Technical characteristics

#### Electric current

Rated current	13 A
---------------	------

#### Voltage

Rated voltage	250 V
---------------	-------

#### Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

#### Safety

Ingress Protection (IP) class	IP66
-------------------------------	------

#### Dimensions

Height	116.50 mm
Width	146 mm
Depth	88.25 mm

#### Materials

Colour	Light grey
Surface finish	Glossy
Material	Polycarbonate (PC)

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	No
With signal lamp	No

#### Accessories

Has labelling field	No
---------------------	----

#### Capacity

Number of modules	0
-------------------	---

#### Texts

Imprint	Without imprint
---------	-----------------

Cover	Full cover plate
Wiring	With double earth connection
Protection	Enhanced contact protection
<b>Cover, door</b>	
Type of lid	Hinged cover falls back, manual clip-in