



WXPSS82

## IP66 Twin 13A Double Pole Switched Socket

### Technical characteristics

#### Architecture

Fixing mode flush-mounting

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Rated current 13 A

#### Dimensions

Depth 88.25 mm

Height 116.5 mm

Width 146 mm

#### Cover, door

Cover Full cover plate

#### Materials

Colour light grey

Material Polycarbonate (PC)

Surface appearance glossy

Type of surface treatment untreated

#### Connection

Type of connection screw

#### Cable

Wiring with double earth connection

#### Safety

Protection index IP IP66

Protection Enhanced contact protection