



### SP&N A Boards

Modules	Dimensions			Fixing Centres		Knockout Size	N° of Knockouts				
	Width	Height	Depth	A	B		Top	Bottom	Left	Right	Back
8	254	236	125	186	150	ø 20	3	3	-	-	-
						ø 32	1	1	1	1	-
						ø 25	1	1	-	-	-
						25 x 50	-	-	-	-	3
12	326	236	125	258	150	ø 20	6	6	-	-	-
						ø 32	1	1	1	1	-
						ø 25	1	1	-	-	-
						25 x 50	-	-	-	-	5
16	398	236	125	330	150	ø 20	8	8	-	-	-
						ø 32	1	1	1	1	-
						ø 25	1	1	-	-	-
						25 x 50	-	-	-	-	7
22	505	236	125	437	150	ø 20	11	11	-	-	-
						ø 32	1	1	1	1	-
						ø 25	1	1	-	-	-
						25 x 50	-	-	-	-	9
2 x 12	326	472	125	258	388	ø 20	6	6	-	-	-
						ø 32	1	1	2	2	-
						ø 25	1	1	-	-	-
						25 x 50	-	-	-	-	6
2 x 16	398	472	125	330	388	ø 20	8	8	-	-	-
						ø 32	1	1	2	2	-
						ø 25	1	1	-	-	-
						25 x 50	-	-	-	-	8
2 x 22	505	472	125	437	388	ø 20	11	11	-	-	-
						ø 32	1	1	2	2	-
						ø 25	1	1	-	-	-
						25 x 50	-	-	-	-	10
3 x 22	505	708	125	437	624	ø 20	11	11	-	-	-
						ø 32	1	1	3	3	-
						ø 25	1	1	-	-	-
						25 x 50	-	-	-	-	15

### Invicta 3 SP&N A Boards

	Dimensions (mm)			Fixing Centres (mm)		
	Height	Width	Depth	A	B	C
JK114A/AG	300	465	107.7	350	35	228
JK129A/AG	450	465	107.7	330	35	378

