



Characteristics	JK1**	JK2**
Standards	Designed, manufactured and tested to BS EN 61439-3	Designed, manufactured and tested to BS EN 61439-3
Busbar Current Rating	125A	250A
Busbar Type	Fully shrouded copper	Fully shrouded copper
Busbar Rating	25kA Conditional	25kA Conditional
Incoming	100A Switch	250A MCS
	125A Switch	250A MCCB
	63A contactor AC3	160A contactor AC3
	100A contactor AC3	
	Direct connection	Direct connection
	RCCB incomers	
Outgoing Ways	4, 6, 8, 12, 16, 18, 24 Triple pole outgoing ways	8, 12, 16, 18, 24 Triple pole way outgoing ways
Outgoing Protection	Type B MCB (6A to 63A, 1P & 3P) Type C, D MCB, (0.5A to 63A, 1P & 3P) 1Mod and 2Mod RCBO	Type B MCB (6A to 63A, 1P & 3P) Type C, D MCB, (0.5A to 63A, 1P & 3P) 1Mod and 2Mod RCBO
Voltage Rating in AC	230 / 415V	230 / 415V
IP Protection	IP3X to BS EN 60529	IP3X to BS EN 60529
Enclosure Body Type	Steel	Steel
Enclosure Paint Type	Powder Coat Grey White BS4800 00A01	Powder Coat Grey White BS4800 00A01
Cable Entry	Obround protected cable entry points	Obround protected cable entry points
<b>Terminal Connection Capacity</b>		
Incoming Line Terminal	50mm <sup>2</sup>	120mm <sup>2</sup>
Incoming Earth Terminal	M8 stud	M8 stud
Incoming Neutral Terminal	50mm <sup>2</sup> cage or M6 stud	M8 Stud
Outgoing Earth Terminals	16mm <sup>2</sup>	16mm <sup>2</sup>
Outgoing Neutral Terminals	16mm <sup>2</sup>	16mm <sup>2</sup>
Enclosure Earth Stud	M8	M8
<b>Installation</b>		
Mounting	4 x key hole fixing holes plus central top key hole for one fixing hanging / levelling Surface Wall Mount	4 x key hole fixing holes plus central top key hole for one fixing hanging / levelling Surface Wall Mount
Gland Plate	Top and bottom removable	Top and bottom removable
Integrated Locking System	Coin lock as standard, key lock as accessory	Coin lock as standard, key lock as accessory

**Torque Settings**

			Cables >1.5mm <sup>2</sup> Tightening torque (N.m)		Cables ≤1.5mm <sup>2</sup> Tightening torque (N.m)		Cable Stripping (mm)
			Single Cable	Multi Cables	Single Cable	Multi Cable	
<b>Consumer unit terminals</b>							
Earth and neutral terminal bars	2	6.5	2	2	1.5	1.5	10
<b>Isolation</b>							
SB switch disconnectors	2	6.5	3.6	3.6	3.6	3.6	15
<b>Circuit protection</b>							
MTN MCB	2	6.5	2.8	2.8	2.8	2.8	13
NBN/NCN/NDN MCB	2	6.5	2.8	2.8	2.8	2.8	13
RCBO	2	5.5	2.1	2.1	2.1	2.1	13
RCCB	2	5.5	2.8	2.8	2.8	2.8	13