



HNG5010007035B

**Slotted panel trunking made of PPO halogenfree HNG 50x100mm light grey**

**Technical properties**

**Architecture**

Flexible	No
----------	----

**Configuration**

Side wall configuration	Slotted
-------------------------	---------

**Electric current**

Current leak stable	Yes
---------------------	-----

**Dimensions**

Trunking height	50 mm
-----------------	-------

Length	2000 mm
--------	---------

Trunking width	100 mm
----------------	--------

Slot width	5 mm
------------	------

Tongue width	7.5 mm
--------------	--------

**Cover, door**

Lid shape	loose
-----------	-------

**Materials**

Colour	light grey
--------	------------

Material group	plastic
----------------	---------

Type of surface treatment	untreated
---------------------------	-----------

**Installation, mounting**

Base punching	EN 50085-2-3:1999
---------------	-------------------

Fixing type	bottom punching
-------------	-----------------

**Cable**

Number of wires 1,5 mm <sup>2</sup> - 40% filling degree	192
--	-----

Internal/useful cross section	4105 mm <sup>2</sup>
-------------------------------	----------------------

Number of wires 2,5 mm <sup>2</sup> - 40% filling degree	137
--	-----

Number of wires 1,0 mm <sup>2</sup> - 40% filling degree	267
--	-----

**Standards**

European directive RoHs	voluntary compliance
-------------------------	----------------------

UL 94 classification	V1
----------------------	----

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
<b>temperatur</b>	
Ambient temperature	-25...90 °C