



38112089

Rot. switch f. blinds 1pole centre plate, rot. knobs, R.classic, p.white glossy

Technical properties

Architecture

Type of control unit	Rotative
Fixing mode	flush-mounting

Functions

Function	only push-button function
----------	---------------------------

Configuration

Switch mode	with neutral position
-------------	-----------------------

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Rated current	10 A

Electric current

Switching current	10 A
-------------------	------

Dimensions

Depth	58.4 mm
-------	---------

Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Plastic/metal

Installation, mounting

Installation mode	for screw fastening
-------------------	---------------------

Connection

Type of connection	with screw terminals
--------------------	----------------------

Use

Differentiation characteristic 2 - Sales	Rotary knobs
--	--------------

Safety

Protection index IP	IP20
---------------------	------

Identification

Main design line	Serie R.classic
------------------	-----------------