ATA205009010

Trunking 20x50,L=2,0m,pure white

Technical properties

Configuration

Antibacterial treatment	No

Connectivity

Trunking coupling	without coupler

Dimensions

Trunking height	20 mm
Length	2000 mm
Trunking width	52 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	5
Maximum number of cables (Ø 11 mm, 50% fill)	5

Cover, door

Lid shape	premounted

Materials

RAL colour	RAL 9010 - Pure white
Material	PVC
Material group	plastic
Type of surface treatment	untreated
Transparent	No

Installation, mounting

Base punching	Without base punching

Cable

Number of wires 1,5 mm² - 40% filling degree	69
Internal/useful cross section	900 mm²
Number of wires 2,5 mm² - 40% filling degree	51

Equipment

Number of fix dividers	0
Number of plugable separators	0
Compartment quantity	1
Cable retainers per meter	2

Standards

European directive RoHs	voluntary compliance

Safety

Protection index IP	IP40
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

Use conditions

Operating temperature	-5…65 °C