



395619

**Pullcord push-button, change-over contact sep. signal contact, light control**

**Technical characteristics**

**Architecture**

Type of control unit	pull cord
----------------------	-----------

**Configuration**

Switch mode	change-over contact, with separate signal contact
Antibacterial treatment	No

**Compatibility**

IFTTT support available	No
-------------------------	----

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC

**Electric current**

Momentary-contact current	10 A
---------------------------	------

**Dimensions**

Depth	42 mm
Insertion depth	31.2 mm
Contact spacing	> 3 mm
Height	71 mm
Width	71 mm

**Length**

Long pullcord	14 cm
---------------	-------

**Materials**

Material	Plastic/metal
Surface appearance	matt

**Installation, mounting**

Installation mode	for wall and ceiling mounting, with spreader claws
-------------------	--

**Connection**

Connection terminals	according to IEC 60669-1
Connection terminals	according to VDE 0632-1
Type of connection	with plug-in terminals

**Equipment**

Lighting	for lighting and monitoring circuit
----------	-------------------------------------

<b>Use cases</b>	
Application	Light control, Hospital application
<b>Safety</b>	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
<b>Identification</b>	
Application, usage	Light control
Main design line	Light control
<b>Instructions</b>	
Information text	spreader claws, insulated to the supporting ring, self-resetting