



BRP651003HLAN



External corner for BRP/BRHP/BRAP 65x100mm halogen free alu finish

Technical characteristics

Architecture

Fixing mode	Clamping
-------------	----------

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Product compatibility	BRP / BRAP
-----------------------	------------

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	68 mm
Length	40 mm
Trunking width	100 mm

Cover, door

Lid mounting	External
Lid with softlip	-
Number of lids mountable	1

Materials

Colour	aluminium
Material	PC-ABS
Material group	plastic

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	85 / 95 °
-------------	-----------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP40
REACH conform	Yes

RoHS conform	Yes
Impact strength	IK07
temperatur	
Ambient temperature	-30...90 °C