JHF80408BG

800A 12 Way Panelboard 4*250A + 8*125A Glazed Door

Technical characteristics

Architecture

Fixing mode	surface-mounting

Dimensions

Depth of installed product	220 mm
Height of installed product	2050 mm
Width of installed product	900 mm

Cover, door

Type of door closing	Quarter turn lock
Interlockable	No

Materials

RAL colour	RAL 7035 - Light grey
Material	Steel

Equipment

Can be accessorized	Yes

Standards

European directive WEEE	concerned

Safety

Protection class	isol.class I