

JK124BGSPD

125A 24 Way TPN Board with 4 pole SD & Type II SPD Glazed

Technical characteristics

Architecture

Fixing mode	surface-mounting

Main electrical features

Frequency	50 Hz

Dimensions

Depth of installed product	132.5 mm
Height of installed product	1250 mm
Width of installed product	465 mm

Cover, door

Type of door closing	Quarter turn lock
Interlockable	Yes

Materials

Colour	RAL 7035
RAL colour	RAL 7035 - Light grey
Material	Steel

Equipment

Can be accessorized	Yes

Standards

European directive WEEE	concerned

Safety

Protection index IP	IP30
Protection class	isol.class I

Use conditions

Operating temperature	50...-10 °C