

SM400

Analogue ammeter 0-400A indirect reading

Technical characteristics

Architecture

Fixing mode	Din-Rail

Voltage

Rated insulation voltage	2000 V

Dimensions

Depth of installed product	54 mm
Height of installed product	85 mm
Width of installed product	70 mm

Power

Power consumed	1.1 VA
Total power loss under IN	1.1 W

Connection

Connection cross-sect. flexible conductor	1 / 6mm²
Connection cross-sect. rigid cable	1,5 / 10mm²

Safety

Protection index IP	IP20

Use conditions

Operating temperature	-25…50 °C