

TD250

**4-fold solar push button white with FPL**

**Technical characteristics**

| **Architecture** | |
|---|---|
| Number of keys | 2 |
| Fixing mode | surface-mounting |

| **Dimensions** | |
|---|---|
| Depth of installed product | 12 mm |
| Height of installed product | 80.5 mm |
| Dimensions (LLxwwxhh) | 80,5 x 80,5 x 12 mm |
| Width of installed product | 80.5 mm |

| **Materials** | |
|---|---|
| Colour | white |

| **Accessories included** | |
|---|---|
| Inscribable, with labelling field | Yes |

| **Equipment** | |
|---|---|
| Number of channels | 4 |

| **Safety** | |
|---|---|
| Protection index IP | IP30 |

| **Use conditions** | |
|---|---|
| Operating temperature | 0…45 °C |