

VM306AH

6 Way 100A 30mA Type A RCCB Incomer

Technical characteristics

Architecture	
Fixing mode	surface-mounting

Dimensions	
Depth of installed product	102 mm
Height of installed product	240 mm
Width of installed product	221 mm

Cover, door	
Type of door closing	non keylock
Interlockable	No

Materials	
Material	Steel
Type of surface treatment	powder-coated

Equipment	
Number of rows	1
Can be accessorized	Yes

Standards	
European directive WEEE	not concerned