



VM908CUSPD

**Design 30 , 8 way Configureable HI 100A Sw 2\*100A 30mA RCCB Type A SPD**

**Technical characteristics**

**Architecture**

Fixing mode	surface-mounting
-------------	------------------

**Main electrical features**

Rated operational voltage Ue	230 V
Frequency	50 Hz

**Dimensions**

Depth of installed product	102.5 mm
Height of installed product	240 mm
Width of installed product	364 mm

**Cover, door**

Interlockable	No
---------------	----

**Materials**

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Steel

**Equipment**

Number of rows	1
Can be accessorized	Yes

**Standards**

European directive WEEE	concerned
-------------------------	-----------