VML608CUSPD

Design 10 , 8 way Configureable HI 63A Sw 2*63A 30mA RCCB Type A SPD

Technical characteristics

Architecture

Fixing mode	surface-mounting

Dimensions

Depth of installed product	100 mm
Height of installed product	246 mm
Width of installed product	299 mm

Cover, door

Interlockable	No

Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Steel

Equipment

Number of rows	1
Can be accessorized	Yes

Standards

European directive WEEE	concerned