VML910CUSPDRK

10 Way Hi Integrity 100A Switch 2*100A 30mA Type 2 SPD RKO

Technical characteristics

Architecture

Fixing mode	surface-mounting

Dimensions

Depth of installed product	100 mm
Height of installed product	246 mm
Width of installed product	406 mm

Cover, door

Interlockable	No

Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Steel

Equipment

Number of rows	1
Can be accessorized	Yes

Standards

European directive WEEE	concerned