

VMLA90405H

Dual Row 100A Sw, 2*100A 30mA RCCB, 4+5 Way, 2 pole busbar, ARC Fault

Technical characteristics

Architecture

Fixing mode	surface-mounting

Main electrical features

Frequency	50 Hz

Dimensions

Depth of installed product	100 mm
Height of installed product	486 mm
Width of installed product	299 mm

Cover, door

Type of door closing	non keylock
Interlockable	No

Materials

Colour	white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Steel

Equipment

Number of rows	2
Can be accessorized	Yes

Standards

European directive WEEE	concerned

Safety

Protection class	isol.class II