

VSR914CUSPD

14w Hi Integrity 100A Switch 2*100A 30mA RCCB Type 2 SPD

Technical characteristics

Architecture

Fixing mode	flush-mounting

Main electrical features

Frequency	50 Hz

Dimensions

Depth of installed product	105 mm
Height of installed product	284 mm
Width of installed product	539 mm

Cover, door

Type of door closing	non keylock
Interlockable	No

Materials

Colour	RAL 9010
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Steel

Equipment

Number of rows	1
Can be accessorized	Yes

Standards

European directive WEEE	concerned