


WFS51PBB

Technical characteristics

Architecture

Fixing mode	flush-mounting

Main electrical features

Nominal voltage	250 V
Rated voltage	220...230 V AC
Rated current	5 A

Dimensions

Depth	25 mm
Height	86 mm
Width	86 mm

Cover, door

Cover	Full cover plate

Materials

Material	stainless steel
Type of surface treatment	Anodised

Connection

Type of connection	screw

Safety

Protection index IP	IP20
Protection	Enhanced contact protection

Use conditions

Insert	insert, black