

WPSS82BKOW

**2 Gang Double Pole Switched Socket & Back Box with Knockouts White**

## Technical characteristics

### Architecture

| | |
|---|---|
| Fixing mode | flush-mounting |

### Main electrical features

| | |
|---|---|
| Nominal voltage | 250 V |
| Rated voltage | 250 V AC |
| Rated current | 13 A |

### Dimensions

| | |
|---|---|
| Depth | 53.2 mm |
| Height | 86 mm |
| Width | 146 mm |

### Cover, door

| | |
|---|---|
| Cover | Full cover plate |

### Materials

| | |
|---|---|
| Colour | white |
| Material | Steel |

### Connection

| | |
|---|---|
| Type of connection | screw |

### Safety

| | |
|---|---|
| Protection index IP | IP20 |
| Protection | Enhanced contact protection |