

WRSS82PSB-USBS

13A 2 Gang Double Pole Switched Socket c/w Twin USB Ports Polished Steel Black

Technical characteristics

Architecture

Fixing mode	flush-mounting

Main electrical features

Nominal voltage	250 V
Rated voltage	220...230 V AC

Dimensions

Depth	39.1 mm
Height	86 mm
Width	146 mm

Cover, door

Cover	Full cover plate

Materials

Colour	silver optics
Material	stainless steel
Type of surface treatment	Other

Connection

Type of connection	screw

Safety

Protection index IP	IP20
Protection	Enhanced contact protection

Use conditions

Insert	insert, black