



DNG3703707030B

Slotted panel trunking made of PVC DNG 37x37mm stone grey

Technical properties

Architecture

Flexible	No
----------	----

Configuration

Side wall configuration	Slotted
-------------------------	---------

Electric current

Current leak stable	Yes
---------------------	-----

Dimensions

Trunking height	37 mm
-----------------	-------

Length	2000 mm
--------	---------

Trunking width	37 mm
----------------	-------

Slot width	5 mm
------------	------

Tongue width	7.5 mm
--------------	--------

Cover, door

Lid shape	loose
-----------	-------

Materials

Colour	stone grey
--------	------------

Material group	plastic
----------------	---------

Type of surface treatment	untreated
---------------------------	-----------

Installation, mounting

Base punching	DIN 43659
---------------	-----------

Fixing type	bottom punching
-------------	-----------------

Cable

Number of wires 1,5 mm ² - 40% filling degree	48
--	----

Internal/useful cross section	1036 mm ²
-------------------------------	----------------------

Number of wires 2,5 mm ² - 40% filling degree	35
--	----

Number of wires 1,0 mm ² - 40% filling degree	67
--	----

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

UL 94 classification	V0
----------------------	----

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Fireproof classification	M1