



HA7100060

Slotted panel trunking halogenfree HA7 100x60mm light grey

Technical properties

Architecture

Flexible No

Configuration

Side wall configuration Slotted

Electric current

Current leak stable Yes

Dimensions

Trunking height 100 mm

Length 2000 mm

Trunking width 60 mm

Slot width 6 mm

Tongue width 6.5 mm

Cover, door

Lid shape loose

Materials

Colour light grey

RAL colour RAL 7035 - Light grey

Material PC-ABS

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching EN 50085-2-3:1999

Fixing type bottom punching

Cable

Number of wires 1,5 mm² - 40% filling degree 198

Internal/useful cross section 4988 mm²

Number of wires 2,5 mm² - 40% filling degree 142

Number of wires 1,0 mm² - 40% filling degree 275

Standards

Approvals EN50085-2-3

European directive RoHS voluntary compliance

Safety

Fireproof classification

M1

temperatur

Ambient temperature

-25...90 °C