



M5691



Flexible slotted panel trunking Polyamid halogenfree 20mm Länge=0,5m light grey

Technical properties

Architecture

Flexible	Yes
----------	-----

Configuration

Side wall configuration	Slotted
-------------------------	---------

Electric current

Current leak stable	Yes
---------------------	-----

Dimensions

Length	500 mm
Slot width	8 mm
Tongue width	4.5 mm

Cover, door

Lid shape	none
-----------	------

Materials

Colour	light grey
Material	Polyamid (PA)
Material group	plastic
Type of surface treatment	untreated

Installation, mounting

Base punching	With base punching
---------------	--------------------

Cable

Number of wires 1,5 mm ² - 40% filling degree	18
Internal/useful cross section	154 mm ²
Number of wires 2,5 mm ² - 40% filling degree	13
Number of wires 1,0 mm ² - 40% filling degree	20

Standards

European directive RoHS	voluntary compliance
UL 94 classification	V0

Safety

REACH conform	Yes
RoHS conform	Yes

Halogen free	Yes
--------------	-----

temperatur

Ambient temperature	-25...90 °C
---------------------	-------------