LNH0063M

**HRC LV fuse NH000 gG AC500V 63A double indicator with live gripping-lugs**

## Technical properties

### Architecture

| | |
|---|---|
| Curve | gG |

### Fuse

| | |
|---|---|
| Fuse size | NH000 |
| Fuse characteristics | gG |

### Voltage

| | |
|---|---|
| Type voltage supply | AC/DC |

### Electric current

| | |
|---|---|
| Rated current | 63 A |

### Use conditions

| | |
|---|---|
| Insulated | No |

### Main electrical attributes

| | |
|---|---|
| Rated short-circuit breaking capacity Icn AC according to IEC 60898-1 | 120 kA |

### Power

| | |
|---|---|
| Total power loss under IN | 5,40 W |

### Dimensions

| | |
|---|---|
| Height | 58,50 mm |
| Width | 21 mm |
| Depth | 79 mm |