WBHP1S

Allure Single GPO 10A

Technical properties

Configuration	
Number of modules	1

Main electrical features	
Nominal voltage	250 V AC
Frequency	50 Hz

Electric current	
Rated current	10 A

Materials	
Colour	white

Installation, mounting	
Entries	cable entries bevelled
Mounting type	flush-mounted
Installation mode	for screw fastening

Scope of delivery	
Scope of delivery	supplied with standard tapered point 32 mm fixing screws

Equipment	
Number of socket outlets switchable	1
With transparent product label holder	No

Safety	
IK protection code against mecanical impacts	IK08
REACH conform	Yes
RoHS conform	Yes
Protection	without enhanced contact protection

Identification	
Main design line	Allure