FR26G1

Steel enclosure, Univers, IP55, CL1, 1850x1550x400mm, plinth H100 mm

Technical properties

Dimensions	
Height	1,950 mm
Width	1,550 mm
Depth	400 mm
Thickness of sidewall	1.50 mm

Safety	
Ingress Protection (IP) class	IP55
Protection class	Isolation class I
Locking type	Without lock
Impact resistance IK	IK10

Equipment	
Number of section in width	6
Number of flange plate openings	12
Number of rows	12

Installation, mounting	
Mounting on	Floor mounting
Suitable for outdoor usage	No

Materials	
Colour	Light grey
RAL code	7035
Treatment	Powder coated
Material	Steel
Surface finish	Mat

Cover, door	
Number of cabinet doors	2
Number of locks	1
Door/cover is transparent	No

Electric current	
Rated current	800 A

Voltage	
Nominal voltage	690 - 690 V