KDN363B

Insulated busbar 3P 63A fork 10mm² 57M

Technical properties

Electric current

Rated current	63 A

Architecture

Number of poles	3

Dimensions

Length	1,000 mm

Voltage

Rated impulse withstand voltage Uimp	4,500 V

Connection

Cross-section rigid conductor	10 mm²
Connector/plug type	Phase busbar with fork

Capacity

Number of modules	57