KDN380A

Insulated busbar 3P 80A fork 16mm² 12M

Technical properties

Electric current	
Rated current	80 A
Architecture	
Number of poles	3
Dimensions	
Length	210 mm
Voltage	
Rated impulse withstand voltage Uimp	4,500 V
Connection	
Cross-section rigid conductor	16 mm²
Connector/plug type	Phase busbar with fork
Capacity	
Number of modules	12